

TECHNICAL DATA GL 265



Similar to image

AREAS OF APPLICATION:

- Soldering (multi-site extraction)
- Laser processing
- Processes for working with adhesive/moist dusts
- Processes for working with vapours/gases
- Low-noise environments

INCLUDES:


- Fully assembled (incl. the filter configuration of your choice)
- 4 wheels for mobile use
- Power cable

TECHNICAL SPECIFICATIONS	UNIT	STANDARD	Z	A	ZA	TZA	MP
Unimpeded air flow rate	m³/h	max. 560	max. 560	max. 560	max. 560	max. 560	max. 560
Effective air flow rate	m³/h	180-480	180-480	180-480	180-480	180-480	180-480
Max. static pressure	Pa	4000	4000	4000	4000	4000	4000
Voltage	V	230/120	230/120	230/120	230/120	230/120	230/120
Frequency	Hz	50/60	50/60	50/60	50/60	50/60	50/60
Power input	kW	0.24	0.24	0.24	0.24	0.24	0.24
Protection class	-	1	1	1	1	1	1
Motor and drive system	-	brushless motor					
Noise level	db(A)	ca. 53	ca. 53	ca. 53	ca. 53	ca. 53	ca. 53
Serial interface	D-sub	25-pin	25-pin	25-pin	25-pin	25-pin	25-pin
Weight	kg	ca. 70	ca. 70	ca. 70	ca. 90	ca. 110	ca. 65
Dimensions (Height)	mm	750	750	750	1020	1290	890
Dimensions (WidthxDepth)	mm	350x655	350x655	350x655	350x655	350x655	350x655
DN 50 intake socket	number	3	3	3	3	3	3
DN 100 intake socket	number	2	2	2	2	2	2
DN 125 intake socket	number	1	1	1	1	1	1
Colour	RAL	7035	7035	7035	7035	7035	7035

FILTER CONFIGURATION

	Pre-filter mat (F5)	✓	-	✓	-	-	-
T	Pocket filter (F5/F6)	-	-	-	-	✓	-
MP	MP-TEC filter (F7)	-	-	-	-	-	✓
Z	Z-line panel filter (F7)	-	✓	-	✓	✓	-
	Particle filter (H13)	✓	✓	-	✓	✓	✓
A	Activated carbon/BAC filter	26 liter	-	45 liter	45 liter	45 liter	-

ORDER DATA GL 265




STANDARD

DESCRIPTION	ART.-NO.
GL 265 230V 50/60Hz	90136
GL 265 120V 50/60Hz	90150

REPLACEMENT FILTERS

Pre-filter mat	10001	1
Z-line panel filter	-	
Particle filter	10009	2
Activated carbon/BAC	10046	3




Z

DESCRIPTION	ART.-NO.
GL 265 230V 50/60Hz	90153
GL 265 120V 50/60Hz	90154

REPLACEMENT FILTERS

Pre-filter mat	-	
Z-line panel filter	14997	1
Particle filter	10009	2
Activated carbon/BAC	-	




A

DESCRIPTION	ART.-NO.
GL 265 230V 50/60Hz	90151
GL 265 120V 50/60Hz	90152

REPLACEMENT FILTERS

Pre-filter mat	10001	1
Z-line panel filter	-	
Particle filter	-	
Activated carbon/BAC	12052	2




ZA

DESCRIPTION	ART.-NO.
GL 265 230V 50/60Hz	90155
GL 265 120V 50/60Hz	90156

REPLACEMENT FILTERS

Pocket filter	-	
MP-TEC filter	-	
Z-line panel filter	14997	1
Particle filter	10009	2
Activated carbon/BAC	12052	3




TZA

DESCRIPTION	ART.-NO.
GL 265 230V 50/60Hz	90157
GL 265 120V 50/60Hz	90158

REPLACEMENT FILTERS

Pocket filter	12740	1
MP-TEC filter	-	
Z-line panel filter	14997	2
Particle filter	10009	3
Activated carbon/BAC	12052	4



MP

DESCRIPTION	ART.-NO.
GL 265 230V 50/60Hz	90295
GL 265 120V 50/60Hz	90296

REPLACEMENT FILTERS

Pocket filter	-	
MP-TEC filter	13310	1
Z-line panel filter	-	
Particle filter	10009	2
Activated carbon/BAC	-	